

# ALPHA® OM-338-PT

Fine Feature, Zero Halogen, Pin-Testable Lead-Free Solder Paste

## DESCRIPTION

**ALPHA OM-338-PT** is a lead-free, no-clean solder paste designed for a broad range of applications. **ALPHA OM-338-PT's** broad processing window is designed to minimize transition concerns from tin/lead to lead free solder paste. This material is engineered to deliver the comparable performance to a tin lead process. **ALPHA OM-338-PT** yields excellent print capability performance across various board designs; particularly with ultra-fine feature repeatability (11 mil squares) and high "through-put" applications. **ALPHA OM-338-PT** is formulated to offer increased in-circuit pin test yields versus OM-338 without compromising electrical reliability.

Outstanding reflow process window delivers good soldering on CuOSP with excellent coalescence on a broad range of deposit sizes, excellent random solder ball resistance and mid-chip solder ball performance. **ALPHA OM-338-PT** is formulated to deliver excellent visual joint cosmetics. Additionally, **ALPHA OM-338-PT's** capability of IPC Class III for voiding and ROL0 IPC classifications ensures maximum long-term product reliability.

*\*Although the appearance of these lead-free alloys will be different to that of tin-lead, with mechanical reliability equal to or greater than with that of tin-lead or tin-lead-silver.*

## FEATURES & BENEFITS

- Maximizes reflow yield for lead-free processing, allowing full alloy coalescence at circular dimensions as small as 0.225mm (0.011") with 0.100mm (4mil) stencil thickness.
- Excellent print consistency with high process capability index across all board designs.
- Print speeds of up to 150mm/sec (6"/sec), enabling a fast print cycle time and a high throughput.
- Wide reflow profile window with good solderability on various board / component finishes.
- Excellent solder and flux cosmetics after reflow soldering
- Reduction in random solderballing levels, minimizing rework and increasing first time yield
- Excellent pin-test yield for single and double reflow.
- Meets highest IPC 7095 voiding performance classification of Class III.
- Excellent reliability properties, halide-free material
- Compatible with either nitrogen or air reflow

# ALPHA<sup>®</sup> OM-338-PT

Fine Feature, Zero Halogen, Pin-Testable Lead-Free Solder Paste

## PRODUCT INFORMATION

<u>Alloys:</u>	SAC305, SAC357, SAC387, SAC396, SAC405 SACX Plus™ 0307 SMT, & SACX Plus™ 0807 SMT e1 alloys per JESD97 Classification
<u>Powder Size:</u>	Type 3, Type 4, & Type 4.5
<u>Residues:</u>	Approximately 5% by (w/w)
<u>Packaging Sizes:</u>	500 gram jars, 6" & 12" cartridges, DEK ProFlow® cassettes, and 10cc and 30cc dispense syringes
<u>Flux Gel:</u>	<b>ALPHA OM-338-PT</b> Flux Gel is available in 10cc or 30cc syringes for rework applications
<u>Lead Free:</u>	Complies with RoHS Directive 2011/65/EU

NOTE 1: For other alloys, powder size and packaging sizes, contact your local Alpha Sales Office.

## SAFETY

While the **ALPHA OM-338-PT** flux system is not considered toxic, its use in typical reflow will generate a small amount of reaction and decomposition vapors. These vapors should be adequately exhausted from the work area. Consult the SDS for all safety information ([www.AlphaAssembly.com](http://www.AlphaAssembly.com)).

**ALPHA OM-338-PT** should be stored in a refrigerator upon receipt at (1 to 10)°C, (34-50)°F. **ALPHA OM-338-PT** should be permitted to reach room temperature before unsealing its package prior to use (see handling procedures on page 3). This will prevent moisture condensation build up in the solder paste.

## APPLICATION

Formulated for both standard and fine pitch stencil printing, at print speeds of between 25mm/sec (1"/sec) and 150mm/sec (6"/sec), with stencil thickness of 0.100mm (0.004") to 0.150mm (0.006"), particularly when used in conjunction with **ALPHA Stencils**. Blade pressures should be 0.18-0.27 kg/cm of blade (1.0 -1.5 lbs/inch), depending upon the print speed. The higher the print speed employed, the higher the blade pressure that is required. The reflow process window will give high soldering yield with good cosmetics and minimized rework.

# ALPHA® OM-338-PT

Fine Feature, Zero Halogen, Pin-Testable Lead-Free Solder Paste

## TECHNICAL DATA

CATEGORY	RESULTS	PROCEDURES/REMARKS
<b>CHEMICAL PROPERTIES</b>		
Activity Level	ROL0	IPC J-STD-004A
Halide Content	Halide free (by titration)	IPC J-STD-004A
Ag Chromate Test	<b>Pass</b>	IPC J-STD-004A
Copper Corrosion Test	<b>Pass</b> , No Evidence of Corrosion	IPC J-STD-004A
<b>ELECTRICAL PROPERTIES</b>		
SIR (IPC 7 days @ 85° C/85% RH)	<b>Pass</b> , 4.1 x 10 <sup>9</sup> ohms	IPC J-STD-004A (Pass ≥ 1 x 10 <sup>8</sup> ohm)
SIR (Bellcore 96 hrs @ 35°C/85%RH)	<b>Pass</b> , 8.4 x 10 <sup>11</sup> ohms	Bellcore GR78-CORE (Pass ≥ 1 x 10 <sup>11</sup> ohm)
Electromigration (Bellcore 96 hrs @ 65°C/85%RH 10V 500 hrs)	<b>Pass</b> , Initial = 3.8 x 10 <sup>9</sup> ohms Final = 1.9 x 10 <sup>9</sup> ohms	Bellcore GR78-CORE (Pass=final > initial/10)
<b>PHYSICAL PROPERTIES (Using 88.5% Metal, Type #3 Powder)</b>		
Color	Clear, Colorless Flux Residue	
Tack Force vs. Humidity	<b>Pass</b> , Change of <1 g/mm <sup>2</sup> over 24 hours at 25%, 50% and 75 % Relative Humidity	IPC J-STD-005
Tack Force vs. Time	<b>Pass</b> , Change of <10% when stored at 25±2°C and 50±10% relative humidity	JIS Z-3284, Annex 9
Viscosity	83.3% metal load for T3 designated M04 for dispensing. 88.5% metal load for T3 designated M15 and 88.5% metal load for T4 designated M16 for printing.	Malcom Spiral Viscometer; 1. J-STD-005
Solderball	<b>Acceptable</b> (SAC 305 and SAC405 alloys)	IPC J-STD-005
Stencil Life	<b>8 hours</b>	@ 50%RH, 23°C (74°F)
Spread	<b>Pass</b>	JIS-Z-3197: 1999 8.3.1.1
Slump	<b>Pass</b>	IPC J-STD-005 (10 min 150°C)

# ALPHA<sup>®</sup> OM-338-PT

Fine Feature, Zero Halogen, Pin-Testable Lead-Free Solder Paste

## HALOGEN STATUS

ALPHA OM-338-PT is a halogen free product and passes the standards listed in the Table below:

Halogen Standards			
Standard	Requirement	Test Method	Status
<b>JEITA ET-7304</b> <i>Definition of Halogen Free Soldering Materials</i>	< 1000 ppm Br, Cl, F in solder material solids	<b>TM EN 14582</b>	Pass
<b>IEC 612249-2-21</b>	Post Soldering Residues contain < 900 ppm each or total of < 1500 ppm Br or Cl from flame retardant source		Pass
<b>JEDEC</b> <i>A Guideline for Defining "Low Halogen" Electronics</i>	Post soldering residues contain < 1000 ppm Br or Cl from flame retardant source		Pass
<b>Halogen Free:</b> No halogenated compounds have been intentionally added to this product			

## PROCESSING GUIDELINES

STORAGE-HANDLING	PRINTING	REFLOW*	CLEANING
<ol style="list-style-type: none"> <li>Refrigerate to guarantee stability @ (1-10)°C, (32-50)°F</li> <li>Shelf life of refrigerated paste is 6 months from the manufacturing date.</li> <li>Paste can be stored for 2 weeks at room temperatures up to 25°C (77°F) prior to use.</li> <li>When refrigerated, warm-up of paste container to room temperature for up to 4 hrs. Paste must be ≥19°C (66°F) before processing. Verify paste temperature with a thermometer to ensure paste is at 19°C (66°F) or greater before setup.</li> <li>Do not remove worked paste from stencil and mix with unused paste in jar. This will alter rheology of unused paste.</li> <li>These are starting recommendations and all process settings should be reviewed independently.</li> <li>Temperature working range (on the stencil): 19°C – 32°C</li> </ol>	<p><b>STENCIL:</b> Recommend <b>ALPHA CUT</b> or <b>ALPHA FORM</b> stencils @ 0.100mm - 0.150 mm (4-6 mil) thick for 0.4 - 0.5 mm (0.016" or 0.020") pitch. Stencil design is subject to many process variables. Contact your local <b>ALPHA Stencil</b> site for advice.</p> <p><b>SQUEEGEE:</b> Metal (recommended)</p> <p><b>PASTE ROLL:</b> 1.5-2.0 cm diameter and make additions when roll reaches 1-cm (0.4") diameter (min). Max roll size will depend upon blade. "Exceeding the maximum diameter may cause curtaining (sticking to the squeegee when it is lifted from the stencil)."</p> <p><b>PRESSURE:</b> 0.5 – 0.7 kg/inch of blade length</p> <p><b>SPEED:</b> 25 - 150mm per second (1 - 8 inches per second).</p> <p>Release speed: within 3- 10 mm/s. Setting done under microscope. Poor release settings: results in icicles or missing paste in small apertures.</p>	<p><b>ATMOSPHERE:</b> Clean-dry air or nitrogen atmosphere.</p> <p><b>PROFILE (SAC Alloys):</b> Acceptable reflow / coalescence and IPC Class III voiding were obtained for the range of profiles depicted below.</p> <p>Note 2: Refer to component and board supplier data for thermal properties at elevated temperatures. Lower peak temperatures require longer TAL for improved joint cosmetics.</p>	<p><b>ALPHA OM-338-PT</b> residue is designed to remain on the board after reflow. If reflowed residue cleaning is required, <b>ALPHA BC-2200</b> aqueous cleaner is recommended. For solvent cleaning, agitation for 5 min in the following cleaners is recommended:</p> <ul style="list-style-type: none"> <li>- <b>ALPHA SM-110E</b></li> <li>- Kyzen Micronox MX2501</li> <li>- ATRON® AC 205 (ZESTRON)</li> </ul> <p>Misprints and stencil cleaning may be done with <b>ALPHA SM-110E, ALPHA SM-440, ALPHA BC-2200</b> and ZESTRON® SD 301 cleaners.</p>

\*See figure 1 for reflow

# ALPHA® OM-338-PT

Fine Feature, Zero Halogen, Pin-Testable Lead-Free Solder Paste

Figure 1: Typical Ramp Reflow Profile for SAC Alloys





Figure 2: Typical Soak Reflow Profile for SAC Alloys



Note 3: These are processing guidelines that were tested in the lab with acceptable performance. Optimization to each board application should still be carried out by users to ensure best results.

# ALPHA® OM-338-PT

Fine Feature, Zero Halogen, Pin-Testable Lead-Free Solder Paste

## CONTACT INFORMATION

To confirm this is the most recent issue, please contact Alpha Assembly Solutions

[www.AlphaAssembly.com](http://www.AlphaAssembly.com)

<p><b>North America</b> 300 Atrium Drive Somerset, NJ 08873, USA 800.367.5460</p>	<p><b>Europe</b> Unit 2, Genesis Business Park Albert Drive Woking, Surrey, GU21 5RW, UK 01483.758400</p>	<p><b>Asia</b> 8/F., Paul Y. Centre 51 Hung To Road Kwun Tong, Kowloon, Hong Kong 852.3190.3100</p>
---	---	---

Also read carefully warning and safety information on the Safety Data Sheet. This data sheet contains technical information required for safe and economical operation of this product. READ IT THOROUGHLY PRIOR TO PRODUCT USE. Emergency directory assistance Chemtrec 1 - 800 - 424 - 9300.

DISCLAIMER: All statements, technical information and recommendations contained herein are based on tests we believe to be reliable, but the accuracy or completeness thereof is not guaranteed. No statement or recommendation shall constitute a representation unless set forth in an agreement signed by officers of seller and manufacturer. NO WARRANTY OR MERCHANTABILITY OR WARRANTY OF FITNESS FOR A PARTICULAR PURPOSE IS MADE. The following warranty is made in lieu of such warranties and all other warranties, express, implied, or statutory. Products are warranted to be free from defects in material and workmanship at the time sold. The sole obligation of seller and manufacturer under this warranty shall be to replace any product defective at the time sold. Under no circumstances shall manufacturer or seller be liable for any loss, damage or expense, direct or consequential, arising out of the inability to use the product. Notwithstanding the foregoing, if products are supplied in response to a customer request that specifies operating parameters beyond those stated above, or if products are used under conditions exceeding said parameters, the customer by acceptance or use thereof assumes all risk of product failure and of all direct, indirect and consequential damages that may result from use of the products under conditions, and agrees to exonerate, indemnify and hold harmless MacDermid Incorporated therefrom. No suggestion for product use nor anything contained herein shall be construed as a recommendation to use any product in infringement of any patent rights, and seller and manufacturer assume no responsibility or liability for any such infringement.

© Registered Trademark of MacDermid Performance Solutions. ™ Trademark of MacDermid Performance Solutions.  
© Platform Specialty Products Corporation and its subsidiaries 2016.